# 21B0-T1-A00D00-00 | CMC21



### Empty CMC21 Thermosiphon Outdoor Equipment Cabinet

The cabinet is designed to house rack mounted equipment. This includes DC power systems, Fiber storage/splice trays, cell site routers, batteries, and other rack mounted equipment. This cabinet provides mechanical and environmental protection for the equipment inside. Cooling of active equipment is achieved by DC rated 150W/k Thermosiphon or 2000W HVAC.

- Excellent Thermal Performance compatible with thermosiphon or HVAC
- Provides mounting space for power distribution, network servers, batteries, or other equipment.
- Front door compatible with Pad Lock.
- Provides flexible access for the cable entrances.
- Optional heater for cold environments.
- Provides 21RU of 19" or 23" Rack Space for Equipment
- Common parts available across the same platform.

#### **Product Classification**

Product Type Outdoor cabinet

Product Series CMC

## General Specifications

Access Front door | Removable panel

Alarm Type Door alarm | HVAC alarms (including high temperature, failure) | S2 module, 20P or

standard and user defined alarms

**Batteries** Not included

**Batteries Supported** 6

Capacity 1000 W Heater

**Color** Gray

Cooling 150 W/k Thermosiphon | 2000W HVAC

**Door Security**Quarter turn lock, puck lock system for rear door | Swing handle, puck lock system for front

door

Mounting H-frame | Pad | Pole | Universal wall mount

Noise Emission, maximum 65 dBA

Rack Type EIA 19 in | EIA 23 in



## 21B0-T1-A00D00-00 | CMC21

Rack Units 21

**Dimensions** 

 Height
 1143 mm | 45 in

 Width
 711.2 mm | 28 in

 Depth
 711.2 mm | 28 in

**Electrical Specifications** 

**Battery String Current, maximum** 170 A-h @ -48 Vdc

**Battery Strings, quantity** 2 @ -48 Vdc

Cooling Capacity 2000 W

**dc Distribution Type** 19" or 23" Rack DC Distribution Panels or DIN Breakers

Voltage -48 Vdc

Material Specifications

Finish Powder coated | UV resistant

Material Type Aluminum

**Environmental Specifications** 

**Operating Temperature**  $-40 \, ^{\circ}\text{C} \text{ to } +46 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +115 \, ^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \, ^{\circ}\text{C} \text{ to } +70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +158 \, ^{\circ}\text{F})$ 

Environmental Space UV resistant for outdoor

Qualification Standards IP55 | Telcordia GR-487

Thermal Compliance GR-487

Packaging and Weights

**Weight, net** 77.111 kg | 170 lb

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

