

VSRA-TS-B



Adjustable V-Stabilizer™ for a Tower, small leg size (2–8 in)

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Pipe, quantity 0

Tower Taper Non-tapered | Tapered

Dimensions

Face Width 4.42 m | 14.5 ft

Length 1524 mm | 60 in

Mounting Diameter, maximum 203.2 mm | 8 in

Mounting Diameter, minimum 50.8 mm | 2 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Clamps | Legs

Packaging quantity 1

Weight, net 32.885 kg | 72.5 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted

VSRA-TS-B

UK-ROHS

Compliant/Exempted

