## VSRDUAL-TS-B-HD



Heavy Duty Dual V-Stabilizer™ for a Tower, small leg size (2–8 in)

#### **Product Classification**

Product Type Reinforcement kit

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2

mm (8 in) OD

Pipe, quantity 0

Tower Taper Non-tapered | Tapered

**Dimensions** 

 Height
 965.2 mm | 38 in

 Length
 1,320.8 mm | 52 in

 Mounting Diameter, maximum
 203.2 mm | 8 in

 Mounting Diameter, minimum
 50.8 mm | 2 in

Material Specifications

Material Type Hot dip galvanized steel

#### Packaging and Weights

Included Clamps | Legs

Packaging quantity 2

**Weight, net** 67.313 kg | 148.4 lb

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted



# VSRDUAL-TS-B-HD

**UK-ROHS** 

Compliant/Exempted

