


# VSRDUALA-TS-B



Adjustable Dual V-Stabilizer™ for a Tower, small leg size (2–8 in)

## Product Classification

**Product Type** Reinforcement kit

## General Specifications

**Mounting** Angle 60°, 203.2 mm (8 in) | Angle 90°, 152.4 mm (6 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

**Pipe, quantity** 0

**Tower Taper** Non-tapered | Tapered

## Dimensions

**Height** 990.6 mm | 39 in

**Length** 1524 mm | 60 in

**Mounting Diameter, maximum** 203.2 mm | 8 in

**Mounting Diameter, minimum** 50.8 mm | 2 in

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamps | Legs

**Packaging quantity** 2

**Weight, net** 49.442 kg | 109 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted

# VSRDUALA-TS-B

---

UK-ROHS

Compliant/Exempted

