# 2121112-2



Fiber Optic Outside Plant Cable, 12-core, CST (Corrugated Steel Tape) Armored, Loose-tube, Gel-filled,  $50/125~\mu m$ , OM4, Multimode, Black cable jacket

- Designed for use in backbone cabling, campus site cabling, outdoor ducts or direct burial cabling applications
- Designed with a gel filled loose tube construction to ensure protection against moisture ingress

#### **Product Classification**

Regional AvailabilityAsia | EMEAPortfolioCommScope®Product TypeFiber OSP cable

Product Series O-CA

### General Specifications

Armor Type Corrugated steel

Cable Type Loose tube

Subunit Type Gel-filled

Filler, quantity 0

Jacket Color Black

Fibers per Subunit, quantity 12

Total Fiber Count 12

#### Dimensions

**Jacket Marking** 

 Cable Length
 2000 m | 6,561.68 ft


 Diameter Over Jacket
 10 mm | 0.394 in

### Representative Image



Meters

## 2121112-2



#### Material Specifications

Jacket Material High density polyethylene (HDPE)

Mechanical Specifications

Minimum Bend Radius, loaded200 mm7.874 inMinimum Bend Radius, unloaded160 mm6.299 in

Tensile Load, short term, maximum 1300 N | 292.252 lbf

Cable Crush Resistance, maximum 30 N/mm | 171.304 lb/in

Flex 25 cycles

**Optical Specifications** 

**Fiber Type** OM4

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 1.00 dB/km @ 1,300 nm | 3.00 dB/km @ 850 nm

Standards Compliance ANSI/TIA-568.E-3 | IEC 60794-1 | TIA-492AAAD (OM4)

**Environmental Specifications** 

**Operating Temperature**  $-20 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \left(-4 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F}\right)$ 

Packaging and Weights

**Cable weight** 100 kg/km | 67.197 lb/kft

Page 2 of 3

# 2121112-2

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

