
760248388 | MPA-NCLCJ50020M-NS



MPO Fanout Cable, polarity A, 12 fiber MPO (unpinned) to LC duplex, Plenum 3mm SM, 20m, with 36" breakout

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber fanout cable assembly

Product Brand MPOptimate®

Product Series MPA

General Specifications

Connector A, quantity 1

Color, boot ABlackColor, connector AGreenConnector B, quantity12Color, boot BBlueColor, connector BBlue

Construction TypePlug-and-play, array cordInterface, Connector AMPO-12/UPC Female

12

 Interface Feature, connector A
 Unpinned

 Interface, Connector B
 LC/UPC

 Jacket Color
 Yellow

Total Fibers, quantity

Dimensions

Cord Length 20 m | 65.617 ft

Optical Specifications

Fiber Mode Singlemode

Fiber Type OS2

COMMSCOPE®

760248388 MPA-NCLCJ50020M-NS

Environmental Specifications

Environmental Space Plenum

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Classification **Agency**

CHINA-ROHS Below maximum concentration value

ROHS Compliant **UK-ROHS** Compliant



Included Products

Fiber indoor cable, Plenum for MPO Light Duty Patchcords, 12 fiber, Singlemode G.657.A2/B2, 760237964 P-012-MP-8G1-F30YL

Feet jacket marking, Yellow jacket color

LC/UPC Connector, Singlemode, Blue, Short Boot 860637435

MPO12, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm 860638318