
# 760248389 | MPA-NCLCJ50025M-NS



MPO Fanout Cable, polarity A, 12 fiber MPO (unpinned) to LC duplex, Plenum 3mm SM, 25m, with 36" breakout

#### **Product Classification**

Regional Availability Latin America | North America

Portfolio CommScope®

**Product Type** Fiber fanout cable assembly

Product Brand MPOptimate®

Product Series MPA

### General Specifications

Connector A, quantity 1

Color, boot ABlackColor, connector AGreenConnector B, quantity12Color, boot BBlueColor, connector BBlue

Construction TypePlug-and-play, array cordInterface, Connector AMPO-12/UPC Female

 Interface Feature, connector A
 Unpinned

 Interface, Connector B
 LC/UPC

 Jacket Color
 Yellow

**Total Fibers, quantity** 12

**Dimensions** 

**Cord Length** 25 m | 82.021 ft

**Optical Specifications** 

Fiber Mode Singlemode

Fiber Type OS2

COMMSCOPE®

# 760248389 | MPA-NCLCJ50025M-NS

### **Environmental Specifications**

Environmental Space Plenum

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ROHS Compliant UK-ROHS Compliant



#### Included Products

760237964 – Fiber indoor cable, Plenum for MPO Light Duty Patchcords, 12 fiber, Singlemode G.657.A2/B2,

P-012-MP-8G1-F30YL Feet jacket marking, Yellow jacket color

860637435 - LC/UPC Connector, Singlemode, Blue, Short Boot

860638318 – MPO12, ULTRA LOW LOSS, FEMALE, Singlemode, GREEN, 3mm