## MCG23RHDXL-12M1296



G23RHDXL PIM OPTIMIZED SPACING High Capacity Monopole platform with extended 10' Spine for RRU Mounting & extended frame for sites requiring increased sector to sector antenna spacing. 2 7/8in OD x 12ft face with (12) 2-7/8in OD x 96in Antenna pipes

- Extended spine for MCG23 RHDXL mounts that decrease PIM from radio relocation PLUS extended frames for increased antenna-to-antenna spacing
- · Increased versatility and stability
- · Updated frame provides higher loading
- More RRU mounting available, reducing need for additional mounts
- · Better load management
- Less structure stress
- Designed to be used in combination with APEX RRU mounts

#### Product Classification

Product Type High capacity monopole sector frame

Product Brand PIM-guard

**Product Series** G2

### General Specifications

**Mounting** Monopole, 381–1270 mm (15–50 in) OD

Pipe, quantity 12
Sectors, quantity 3

#### Dimensions

Width

**Height** 2,438.4 mm | 96 in

**Face Width** 3.81 m | 12.5 ft

**Pipe Length** 2,438.4 mm | 96 in

Face Support Pipe Diameter 73.025 mm | 2.875 in

**Mounting Diameter, maximum** 1270 mm | 50 in

Mounting Diameter, minimum 381 mm | 15 in

 Pipe Outer Diameter
 73.025 mm | 2.875 in

 Stand-off Distance
 1,549.4 mm | 61 in

## Material Specifications



Page 1 of 2

3,810 mm | 150 in

# MCG23RHDXL-12M1296

Material Type Hot dip galvanized steel

Mechanical Specifications

**Wind Rating** For Specifications, please contact your local ANDREW representative

Wind Rating Test Method TIA/EIA-222

Packaging and Weights

Included Mounting hardware | Pipe mounts | Plain end pipes (12) | Ring mounts (2) | Sector frames

(3) | Stiff arm

Packaging quantity 1

**Weight, net** 1,399.786 kg | 3086 lb

\* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

