



Outdoor Fibre Optic Cable, 24-fibre, loose tube, MM, OM4

Product Classification

Regional Availability	Australia/New Zealand
Product Type	Fiber OSP cable
Product Series	O-LN

General Specifications

Cable Type	Loose tube
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Meters
Total Fiber Count	24

Mechanical Specifications

Flex	25 cycles
------	-----------

Optical Specifications

Fiber Type	OM4, LazrSPEED®
------------	-----------------

Optical Specifications, Wavelength Specific

Standards Compliance	TIA-492AAAD (OM4)
----------------------	-------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



64624474-24 | O-024-LN-5X-M12NS/PE/PA
