760244960 | OCM1-SA41200S2



OCM1 LGX Style Fiber Optic Splitter Module, FBT, four 1x2 Splitters, singlemode, SC/APC, 50/50 split ratio

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability EMEA | Latin America | North America

 Portfolio
 CommScope®

 Product Type
 Splitter module

 Product Series
 LGX | OCM1

Government RequirementsBuild America Buy America (BABA) compliant*

General Specifications

Device Type Standard VAM

Functionality Splitting

Technology Type Fused biconic tapered

Access Front

Application For use with LGX panels

Circuits, quantity 3

Distribution Type1 x 2 splitterInterface, frontSC/APCInterface, InputSC/APCInterface, OutputSC/APC

Location of Manufacturing Waived per BABA waiver for BEAD Program

Split Ratio Symmetrical

Splitter, quantity 3

Dimensions

 Height
 129.54 mm | 5.1 in

 Width
 27.94 mm | 1.1 in



760244960 | OCM1-SA41200S2

Depth 127 mm | 5 in

Packaging and Weights

Packaging quantity

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

