

Fiber Indoor Cable, LazrSPEED® 1.8 mm Low Smoke Zero Halogen Riser, 2-fiber Zipcord, Multimode OM4, Meter jacket marking, Orange jacket color

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber indoor cable
Product Series	N-ZC


General Specifications

Cable Type	Cordage
Construction Type	Non-armored
Subunit Type	Gel-free
Jacket Color	Orange
Jacket Marking	Meters
Total Fiber Count	2

Dimensions

Height Over Jacket	1.8 mm   0.071 in
Width Over Jacket	3.8 mm   0.15 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	60 mm   2.362 in
Minimum Bend Radius, unloaded	30 mm   1.181 in
Tensile Load, long term, maximum	70 N   15.737 lbf
Tensile Load, short term, maximum	178 N   40.016 lbf
Compression	5 N/mm   28.551 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	300 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	0.74 N-m   6.55 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	25 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	500 m   1,640.42 ft

Optical Specifications

Fiber Type	OM4, LazrSPEED® 550
------------	---------------------

## Environmental Specifications

Installation temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	ANSI/ICEA S-83-596   Telcordia GR-20
Environmental Space	Low Smoke Zero Halogen (LSZH)   Riser

## Environmental Test Specifications

Heat Age	-20 °C to +85 °C (-4 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-20 °C to +70 °C (-4 °F to +158 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	-20 °C to +70 °C (-4 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

## Packaging and Weights

Cable weight	4.8 kg/km   3.225 lb/kft
--------------	--------------------------

## Included Products

CS-5K-TB	–	LazrSPEED® 550 OM4 Bend-Insensitive Multimode Fiber
----------	---	---

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable