## CO-SPL-24LCW-PT SM-SPLX 760258118 |



Product Classification

Splicing cassette, 24LC , 900um, SM Simplex, TIA-576 color codes

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber cassette with pigtails
General Specifications	
Adapter Color	Blue
Interface, front	LC/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	24
Total Ports, quantity, front	12
Dimensions	
Height	28.956 mm   1.14 in
Width	104.648 mm   4.12 in
Depth	165.354 mm   6.51 in
Pigtail Length	1.5 m   4.921 ft
Optical Specifications	
Fiber Mode	Singlemode
Fiber Type	G.652.D and G.657.A1   OS2
Insertion Loss, typical	0.25 dB
Return Loss, minimum	55 dB
Environmental Specifications	

Safety Standard UL

# Packaging and Weights

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025



# 760258118 | CO-SPL-24LCW-PT SM-SPLX

### Packaging quantity

# Regulatory Compliance/Certifications

1

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 2 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: January 14, 2025

