760258123 | CO-SPL-12SAW-PT SM-SPLX



Splicing cassette, 12SC APC, 900um, SM Simplex, TIA-576 color codes

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber cassette with pigtails

General Specifications

Adapter ColorGreenInterface, frontSC/APC

Interface, rear Stranded pigtail

Total Fibers, quantity 12

Total Ports, quantity, front 6

Dimensions

 Height
 28.956 mm | 1.14 in

 Width
 104.648 mm | 4.12 in

 Depth
 165.354 mm | 6.51 in

 Pigtail Length
 1.5 m | 4.921 ft

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D and G.657.A1 | OS2

Insertion Loss, typical0.5 dBReturn Loss, minimum65 dB

Environmental Specifications

Safety Standard UL

Packaging and Weights

COMMSCOPE®

760258123 | CO-SPL-12SAW-PT SM-SPLX

Packaging quantity

1

Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
|--------|----------------|

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

