

UJGMXUCRK

Base Product



Ultra Low Loss ULL Singlemode MPO12 (Pinned) to Unconnectorized Pre-terminated Trunk Cable, 72-Fiber, Rollable Ribbon, Low Smoke Zero Halogen (LSZH, 12 fiber)

Product Classification

Regional Availability	Asia Australia/New Zealand Europe Latin America Middle East /Africa North America
Portfolio	CommScope®
Product Type	Fiber trunk cable assembly
Ordering Note	For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration

General Specifications


Color, boot A	Black
Color, connector A	Green
Construction Type	Rollable ribbon Stranded
Furcation Color	Yellow
Interface, Connector A	MPO-12/APC Male
Interface, Connector B	Unterminated
Jacket Color	Yellow
Polarity	Method B Enhanced (ULL)
Fibers per Subunit, quantity	12
Total Fibers, quantity	72

Dimensions

Cable Assembly Length Range (m)	5 – 999
Cable Assembly Length Range (ft)	15 – 999

UJGMXUCRK

Ordering Tree



Optical Specifications

Fiber Mode	Singlemode
Fiber Type	G.657.A2, TeraSPEED®

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Environmental Space	Low Smoke Zero Halogen (LSZH)

Included Products

860638317	-	MP012, ULTRA LOW LOSS, MALE, Singlemode, GREEN, 3mm
-----------	---	---