FD3-AB072J00JABP2



Enhanced Mini FDH, 72F loaded pole/wall mounted cabinet, SC/APC, PNP splitter capable, Dielectric Loose Tube Cable, 100ft stubs using a 1x72F distribution cable assembly and a 1x24F feeder

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeDry Dielectric - Loose Tube

Color Putty white

Distribution Cables, quantity

Distribution Ports, quantity 72

Fibers per Distribution Cable, quantity 72

Fibers per Feeder Cable, quantity 24

Interface, Input SC

Interface Feature, Input APC

Mounting Pole | Wall

Splitter Slots, quantity 8

Dimensions

 Height
 584.2 mm | 23 in

 Width
 330.2 mm | 13 in

 Depth
 203.2 mm | 8 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Mini

Material Specifications

Finish Powder coated

Material Type Aluminum

COMMSC PE°

FD3-AB072J00JABP2

Environmental Specifications

Environmental Space Above ground | Aerial

Qualification Standards Telcordia GR-3123-CORE | Telcordia GR-3125-CORE

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

