

# FD3-AC144J00TBBP2



FDH 3000 Fiber Distribution Extra Small Pole Mount Cabinet, 72F, SC /APC, 0 splitters, die. LT, 96F stubs, 100 ft, 12F

## Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

## General Specifications

Access	Front
Cable Type	Dry Dielectric - Ribbon
Color	Putty white
Distribution Cables, quantity	1
Distribution Ports, quantity	144
Fibers per Distribution Cable, quantity	144
Fibers per Feeder Cable, quantity	24
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pole

## Dimensions

Height	762 mm   30 in
Width	533 mm   20.984 in
Depth	356 mm   14.016 in
Cable Length	30.48 m   100 ft
Enclosure Size	Extra small

## Material Specifications

Finish	Powder coated
Material Type	Aluminum

# FD3-AC144J00TBBP2

---

## Environmental Specifications

<b>Environmental Space</b>	Aerial
----------------------------	--------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

<b>Packaging Type</b>	Pallet
-----------------------	--------

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

