

XP-2525-OFF



Offset Crossover Plate, joins 2-7/8 in to 2-7/8 in OD round members

Product Classification

Product Type Clamp plate

General Specifications

Mounting Crossover plate

Dimensions

Mounting Diameter, maximum 73.025 mm | 2.875 in

Mounting Diameter, minimum 73.025 mm | 2.875 in

Material Thickness 9.525 mm | 0.375 in

Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Plates | U-bolts

Packaging quantity 1