

# MR3919-000-US | FDSC-GATOR-12F-T



Gator 12F Fiber Optic Splice Closure, Re-enterable, Gel Cable sealing, for up to 12 splices, Build America Buy America (BABA)

- Designed for splicing two loose tube “flat drop” style cables of 1 to 12 fibers in above grade, below grade, and direct buried applications
- Uses gel sealing technology to create a sealed closure system that will fit into confined areas such as small “flowerpot” style handholes
- Incorporates our unique cable hold down and strength member termination features and is capable of holding either fusion or mechanical splices
- Tone wires can also be terminated outside of the closure using the included hardware
- \*CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Product Type</b>	Single-ended, flat fiber closure
<b>Product Series</b>	FDSC GATOR
<b>Government Requirements</b>	Build America Buy America (BABA) coming soon*

## General Specifications

<b>Cable Entry Drop Port Style</b>	Flat
<b>Cable Entry Main Port Style</b>	Flat
<b>Cable Ports Quantity, total</b>	2 round ports
<b>Cable Sealing Type</b>	Compressed gel
<b>Closure Sealing Type</b>	Hinged with latch
<b>Closure Style</b>	Single-ended
<b>Color</b>	Black
<b>Location of Manufacturing</b>	Coming soon
<b>Mounting</b>	Wall
<b>Network Area Type</b>	Drop
<b>Splicing Capacity, Mass Fusion, maximum</b>	12
<b>Splicing Capacity, Single Fusion, maximum</b>	12
<b>Splicing Type, Supported</b>	Mass fusion   Single fusion

# MR3919-000-US | FDSC-GATOR-12F-T

---

## Dimensions

<b>Height</b>	30.48 mm   1.2 in
<b>Width</b>	147.32 mm   5.8 in
<b>Length</b>	190.5 mm   7.5 in

## Environmental Specifications

<b>Environmental Space</b>	Below ground   Buried
----------------------------	-----------------------

## Packaging and Weights

<b>Packaging quantity</b>	10
<b>Packaging Type</b>	Box   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

