

SRC3-U5A1B1BL003-US



NOVUX™ Specialty Range Closure 100, splice only, no adapter, no splitter, 12 splices, SMOUV® 45mm & 12-way ribbon splice protectors, black, 2x NVX-CR-MC-FT-NN cable retention, 2x pre-installed FHD-F01K-0003M, Build America Buy America (BABA)

- Modern drop solution offering providers the agility and flexibility to use it in last-mile fiber network applications, both above and below ground
- Protected from harsh conditions by CommScope's Octopus gel sealing technology
- Agnostic to connectivity technologies: splice, connector, field-installable connector for agility and flexibility
- Identification plate for either QR code or customer logo
- QR code and CommScope cTrak® app for one-click access to all product information
- *CommScope intends to release this product at a future date. At such time, this product will comply with the requirements of the Build America, Buy America Act and/or applicable waivers. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	Asia EMEA Latin America North America
Regional Availability Note	Contact your local CommScope representative for specific availability
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	SRC100
Government Requirements	Build America Buy America (BABA) coming soon*

General Specifications

Cable Capacity, Drop	4 Flat 8.0 x 4.5 mm (0.30 x 0.17 in) 4 Round 1.2–8.0 mm (0.05–0.31 in)
Cable Ports Quantity, total	4 multi-out ports (8 cables)
Cable Sealing Type	Compressed gel
Cable Termination Attachments, quantity	2
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Location of Manufacturing	Coming soon
Mounting	Handhole Partially buried Pedestal Wall/Pole Mount, mounting kit included

SRC3-U5A1B1BL003-US

Network Area Type	Drop
Port Type	No adapter No adapter
Port, quantity	0
Splice Tray Included, quantity	1
Splice Tray Type Included	12-way, heat shrink
Splicing Capacity, maximum	12
Splicing Capacity, Single Fusion, maximum	12
Splicing Type, Supported	Single fusion
Splitter Type	No splitter
Splitter, quantity	0

Dimensions






Height	267 mm 10.512 in
Width	117 mm 4.606 in
Depth	49 mm 1.929 in
Cable Entry Drop Port Diameter	8 mm (0.31 in) mm

Ordering Tree

SRC3-U5A1B1BL003-US



2 cable attachments are supplied.

Cable retention*	Cable Termination Unit (CTU) options				
A None	B 	C 	D 	E 	F 
B NVX-CR-MC-FT-NN	NVX-CR-MC-FT-NN	NVX-CR-MC-RD-NN	NVX-CR-SA-SM-NN	NVX-CR-TI-SM-NN	NVX-CR-DU-FL-NN
C NVX-CR-MC-RD-NN	<ul style="list-style-type: none"> Flat cable Metal clip Range 3 x 5 to 4 x 8 mm 	<ul style="list-style-type: none"> Round cable Metal clip Range 4 to 6.2 mm 	<ul style="list-style-type: none"> Round cable Dia up to 8 mm Strength member Aramide yarns Single layer 	<ul style="list-style-type: none"> Round cable Dia up to 8 mm Aramide yarns Single layer 	<ul style="list-style-type: none"> Round cable Dia up to 6.2 mm Aramide yarns Dual layer Compact length
D NVX-CR-SA-SM-NN					
E NVX-CR-TI-SM-NN					
F NVX-CR-DU-FL-NN					
G 4xNVX-CR-MC-FT-NN					
H 4xNVX-CR-MC-RD-NN					
I 4xNVX-CR-SA-SM-NN					
J 4xNVX-CR-TI-SM-NN					
K 4xNVX-CR-DU-FL-NN					
L 2xNVX-CR-MC-FT-NN and 2xNVX-CR-MC-RD-NN					

Material Specifications

Material Type Impact-resistant polymer

Optical Specifications

Fiber Type G.652.D | G.657.A1 | G.657.A2 | G.657.B3

Environmental Specifications

Operating Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Environmental Space Above ground | Below ground | Direct burial

Qualification Standards IEC 60529, IP68 + 2 m waterhead | IEC 61753-1, category G

UV Resistance UV stabilized

SRC3-U5A1B1BL003-US

Water Resistance

Flash test valve at 2 psi (20 kPa)

Packaging and Weights

Packaging quantity

10

Packaging Type

Box | Carton

Included Products

NVX-CR-MC-FT-NN

–

NOVUX™ Cable Termination Unit (CTU) for flat cables with 3x5 to 4x8 mm diameter, metal clip

NVX-CR-MC-FT-NN



NOVUX™ Cable Termination Unit (CTU) for flat cables with 3x5 to 4x8 mm diameter, metal clip

Product Classification

Regional Availability	Asia EMEA Latin America North America
Product Type	Cable termination kit
Product Brand	NOVUX™
Product Series	CSC

General Specifications

Application	For use with CSC Fiber closures
Color	Black

Packaging and Weights

Packaging quantity	20
Packaging Type	Bag Box

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

