## FD3-AB072J00AABP2-US



Enhanced Mini FDH, 72F loaded pole/wall mounted cabinet, SC/APC, PNP splitter capable, Indoor/Outdoor Dry Dielectric Flat Ribbon Cable, 100ft stubs, using a 1x72F distribution cable assembly and1x24F feeder, Build America Buy America (BABA)\* Coming soon

\*CommScope intends to release this product at a future date. At such time, this product will
comply with the requirements of the Build America, Buy America Act and/or applicable waivers.
 Compliance requirements and waiver applicability vary based on government funding program.
 Check the laws and regulations for your specific program.

### **Product Classification**

Regional Availability North America

**Product Type** Fiber distribution hub

**Product Series** FDH 3000

**Government Requirements**Build America Buy America (BABA) coming soon\*

## General Specifications

**Access** Front

Cable TypeDry Dielectric - Ribbon

**Color** Putty white

Distribution Cables, quantity 1

**Distribution Ports, quantity** 72

Fibers per Distribution Cable, quantity 72

Fibers per Feeder Cable, quantity 24

Interface, Input SC

Interface Feature, Input APC

Location of Manufacturing Coming soon

Mounting Pole | Wall

Splitter Slots, quantity 8

#### **Dimensions**

 Height
 584.2 mm | 23 in

 Width
 330.2 mm | 13 in

**COMMSCOPE®** 

# FD3-AB072J00AABP2-US

 Depth
 203.2 mm | 8 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Mini

Material Specifications

**Finish** Powder coated

Material Type Aluminum

**Environmental Specifications** 

Environmental Space Above ground | Aerial

**Qualification Standards**Telcordia GR-3123-CORE | Telcordia GR-3125-CORE

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet