

# DFJ-2S5-2G



HELIAX® Discrete, 2 single mode fiber, 5 mm, LSZH cable. Plug and play DLC GEN 1.5 to.DLC GEN 1.5

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Wireless Fiber Cable Assemblies
<b>Product Brand</b>	HELIAX®
<b>Product Series</b>	DFJ
<b>Ordering Note</b>	CommScope® Standard Product in Europe

## General Specifications

<b>Construction Type</b>	Discrete fiber tail
<b>Interface, Connector A</b>	DLC plug and play GEN1.5
<b>Interface Feature, connector A</b>	Standard
<b>Interface Body Style, connector A</b>	Flex angle
<b>Interface, Connector B</b>	DLC plug and play GEN1.5
<b>Interface Feature, connector B</b>	Standard
<b>Interface Body Style, connector B</b>	Flex angle
<b>Jacket Color</b>	Black
<b>Total Fibers, quantity</b>	2

## Dimensions

<b>Cable Assembly Length Range (m)</b>	1 – 15
<b>Diameter Over Jacket</b>	5 mm   0.197 in

## Material Specifications

<b>Jacket Material</b>	Low Smoke Zero Halogen (LSZH)
------------------------	-------------------------------

## Mechanical Specifications

<b>Minimum Bend Radius</b>	54 mm   2.126 in
<b>Minimum Bend Radius, furcation</b>	30 mm   1.181 in

## Optical Specifications

# DFJ-2S5-2G

---

<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, typical note</b>	Insertion loss is measured at 1310 and 1550 nm
<b>Insertion Loss, typical</b>	0.5

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +75 °C (-40 °F to +167 °F)
<b>Environmental Space</b>	Outdoor

## \* Footnotes

**Insertion Loss, typical note** Insertion loss is measured at a room temp of +20°C (+68°F)