

RT-NF11-B



PIM-Guard High Capacity Non-Penetrating Roof Frame with Optimized Antenna Spacing 11 ft face, Base Frame Only

Product Classification

Product Type	Non-penetrating roof frame
Product Brand	PIM-guard

General Specifications

Mounting	Non-penetrating
Pipe, quantity	0

Dimensions

Height	2,252.98 mm 88.7 in
Face Width	3.353 m 11 ft
Width	3,352.8 mm 132 in
Length	2.377 m 7.8 ft
Pipe Length	0 mm 0 in
Face Support Pipe Diameter	73.152 mm 2.88 in
Pipe Outer Diameter	73.152 mm 2.88 in

Material Specifications

Material Type	Hot dip galvanized steel
----------------------	--------------------------

Mechanical Specifications

Wind Rating	For Specifications, please contact steelproducts@commscope.com or call 800-255-1479
Wind Rating Test Method	TIA/EIA-222

Packaging and Weights

RT-NF11-B

Included	Ballast tray Frame
Packaging quantity	1
Weight, net	383.6 kg 845.692 lb

* Footnotes

Wind Rating	BWS—Base Wind Speed; FBC—Florida Building Code
--------------------	--