

760253292 | EPX-4U-MOD-ENC-W

EPX 4U sliding panel, accepts (16) G2 style splice cassettes, modules or adapter packs, providing up to 192 duplex LC ports, white

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel Fiber patch/splice panel
Product Series	EPX

General Specifications

Application	Accepts sixteen G2 modular cassettes
Color	White
Intelligence Type	Not iPatch® ready
Interface, front	Unloaded
Module/Adapter Pack Slots, quantity	16
Rack Type	EIA 19 in
Rack Units	4
Shelf Movement	Sliding
Total Fibers, quantity	384
Total Ports, quantity	0

Dimensions

Height	177.8 mm 7 in
Width	482.6 mm 19 in
Depth	412.75 mm 16.25 in

Environmental Specifications

Safety Standard	CSA 22.2 UL 1863
-----------------	--------------------

Packaging and Weights

Packaging quantity	1
Weight, net	7.439 kg 16.4 lb