

# PCA-16-25MM2-2C

---



HELIAX® fiber adaptor, 2 Core DC Power Cable connection. Input Power Cable conductor size as 2.5mm<sup>2</sup>~25mm<sup>2</sup> and Output Power Cable conductor size as 2.5mm<sup>2</sup>~16mm<sup>2</sup>. Shield contact size as 4~6mm<sup>2</sup>. Glands at both ends providing a IP67 weatherproof performance.

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Power adapters
<b>Product Brand</b>	HELIAX®

## General Specifications

<b>Color</b>	Black
--------------	-------

## Material Specifications

<b>Material Type</b>	Polycarbonate ABS (PC-ABS)
----------------------	----------------------------

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +85 °C (-40 °F to +185 °F)
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Flammability Rating</b>	UL 94 V-0
<b>Qualification Standards</b>	IEC 60529, IP67

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---