

UNGLCLCT4

Base Product

Ultra Low Loss ULL TeraSPEED® LC/UPC to LC/UPC Ruggedized fanout Cable, 4-Fiber, LSZH, 8 fiber PmP 2.0 mm Dca

Product Classification

| | |
|-----------------------|--|
| Regional Availability | Asia Australia/New Zealand Europe Latin America Middle East/Africa North America |
| Portfolio | CommScope® |
| Product Type | Ruggedized fanout |
| Product Brand | SYSTIMAX ULL |
| Ordering Note | For additional jacket colors, please contact a CommScope Sales Representative For lengths greater than 999 ft (304 m), orders must be in meters Minimum length may vary based on cable configuration |

General Specifications

| | |
|--------------------------------|----------|
| Color, boot A | Blue |
| Color, connector A | Blue |
| Color, boot B | Blue |
| Color, connector B | Blue |
| Construction Type | Stranded |
| Furcation Color | Yellow |
| Interface, Connector A | LC/UPC |
| Interface Feature, connector A | ULL |
| Interface, Connector B | LC/UPC |
| Interface Feature, connector B | ULL |
| Jacket Color | Yellow |
| Fibers per Subunit, quantity | 8 |
| Total Fibers, quantity | 4 |

Dimensions

| | |
|----------------------------------|----------|
| Cable Assembly Length Range (m) | 3 – 305 |
| Cable Assembly Length Range (ft) | 10 – 999 |

Ordering Tree

UNGLCLCT4

BASE CODE

-

M

.

.

.

.

.

.

Jacket Color

M

Aqua

Breakout Length / Option

| | |
|---|--|
| A | 33 inch breakout, no gland |
| B | 33 inch breakout, with gland |
| D | 12 inch breakout, with gland, pulling grip (side A only) |
| E | 24 inch breakout, no gland |
| F | 24 inch breakout, with gland |
| G | 24 inch breakout, with gland, pulling grip (side A only) |
| H | 48 inch breakout, no gland |
| J | 48 inch breakout, with gland |
| L | 72 inch breakout, no gland |
| M | 72 inch breakout, with gland |
| P | 96 inch breakout, no gland |
| Q | 96 inch breakout, with gland |
| S | 36 inch breakout, no gland |
| T | 36 inch breakout, with gland, pulling grip (side A only) |
| U | 36 inch breakout, with gland |
| V | 60 inch breakout, no gland |
| W | 60 inch breakout, with pulling grip |
| 1 | 33/60 inch breakout, no gland |
| 2 | 33/60 inch breakout, with gland on side A |
| 3 | 33/60 inch breakout, with pulling grip and gland on side A |
| 4 | 23 inch breakout, mounting clips included, no pulling grip on side A |
| 5 | 23 inch breakout, mounting clips included, pulling grip on side A |
| 8 | 24 inch breakout, no gland, pulling grip (side A only) |

Length

UOM

F

Feet

M

Meter

Optical Specifications

Fiber Mode

Singlemode

Environmental Specifications

Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

EN50575 CPR Cable EuroClass Fire Performance

Dca

Environmental Space

Dual Rated LSZH/Riser | Indoor

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

UNGLCLCT4

ROHS

UK-ROHS

Compliant

Compliant



Included Products

- 760245569

N-008-MP-8G1-F08YL/20T/D

860637435
- Fiber indoor cable, Low Smoke Zero Halogen Riser MPO Trunk with 2.0mm Subunits, 8 fiber, Singlemode G.657.A2/B2, Feet jacket marking, Yellow jacket color, Dca flame rating
- LC/UPC Connector, Singlemode, Blue, Short Boot