UGBKIT-0420-T



Tinned Copper Ground Buss Bar, 1/4 in x 4 in x 20 in (6.4 mm x 101.6 mm x 508.0 mm)

Product Classification

Product Type Grounding bar
Product Brand HELIAX®

Ordering Note ANDREW® non-standard product

Dimensions

 Height
 101.6 mm | 4 in

 Length
 508 mm | 20 in

 Material Thickness
 6.35 mm | 0.25 in

Hole Size 7/16 in | 7/16 in x 5/8 in

Hole Distance, center to center 19.05 mm | 0.75 in

Material Specifications

Material Type Tinned copper

Packaging and Weights

 Height, packed
 655.32 mm | 25.8 in

 Width, packed
 121.92 mm | 4.8 in

 Length, packed
 63.5 mm | 2.5 in

Included Galvanized angle adapter | Grounding bar | Insulators | Mounting

brackets | Universal hardware

Packaging quantity 1

Weight, gross 4.6 kg | 10.141 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system



UGBKIT-0420-T

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

GB-HK-DPU – Universal Buss Bar Installation Hardware Kit, UL467

Compliant



GB-HK-DPU



Universal Buss Bar Installation Hardware Kit, UL467 Compliant

Product Classification

Product Type Attachment kit

Product Brand HELIAX®

Ordering Note ANDREW® standard product in the United States and Canada

General Specifications

Accessories Grounding Bars

Packaging and Weights

 Height, packed
 170.18 mm | 6.7 in

 Width, packed
 129.54 mm | 5.1 in

 Length, packed
 99.06 mm | 3.9 in

Included Angle adapters | Drive pin anchor | Insulators, Mounting brackets | Universal hardware

Packaging quantity 1

Weight, gross 2.6 kg | 5.732 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

