# 760237948 | 3298A-B WH 4/23 R1640



3298A-B Category 7A S/FTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1640 ft (500 m) length, reel

#### **Product Classification**

Regional Availability EMEA

**Portfolio** SYSTIMAX®

Product Type Twisted pair cable

General Specifications

Product Number 3298A-B

ANSI/TIA Category 7A

Cable Component Type Horizontal

Cable Type S/FTP (shielded)

Conductor Type, singles Solid

Conductors, quantity 8

Jacket Color White

Pairs, quantity 4

**Transmission Standards** ANSI/TIA-568.2-D | CENELEC EN 50288-9-1 | IEC 61156-5 Cat

7 | ISO/IEC 11801 Class FA

**Dimensions** 

**Cable Length** 500 m | 1,640.42 ft

Cable Length Tolerance ±5%

 Diameter Over Jacket, nominal
 7.493 mm | 0.295 in


 Jacket Thickness
 0.635 mm | 0.025 in

Conductor Gauge, singles 23 AWG

Cross Section Drawing



## 760237948 | 3298A-B WH 4/23 R1640



## **Electrical Specifications**

dc Resistance Unbalance, maximum 2 %

**dc Resistance, maximum** 7.61 ohms/100 m | 2.32 ohms/100 ft

**Delay Skew, maximum** 25 ns

**Mutual Capacitance at Frequency** 4.3 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 76 %

Operating Frequency, maximum 1000 MHz

Operating Voltage, maximum 80 V

Material Specifications

Conductor MaterialBare copperInsulation MaterialPolyolefin

Jacket Material Low Smoke Zero Halogen (LSZH)

Shield (Braid) Material Tinned copper

Shield (Tape) Material Polyester/Aluminum shield

Mechanical Specifications

**Pulling Tension, maximum** 11.34 kg | 25 lb

**Environmental Specifications** 

Installation temperature  $0 \,^{\circ}\text{C}$  to +50  $^{\circ}\text{C}$  (+32  $^{\circ}\text{F}$  to +122  $^{\circ}\text{F}$ )

Operating Temperature  $-20 \,^{\circ}\text{C}$  to +60  $^{\circ}\text{C}$  (-4  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

**COMMSCOPE®** 

# 760237948 | 3298A-B WH 4/23 R1640

Acid Gas Test Method EN 50267-2-3

**EN50575 CPR Cable EuroClass Fire Performance** B2ca

EN50575 CPR Cable EuroClass Smoke Rating s1

EN50575 CPR Cable EuroClass Droplets Rating d1

EN50575 CPR Cable EuroClass Acidity Rating a1

Environmental Space Low Smoke Zero Halogen (LSZH)

Smoke Test Method IEC 61034-2

Packaging and Weights

**Cable weight** 64.125 kg/km | 43.09 lb/kft

Packaging Type Reel

## Regulatory Compliance/Certifications

#### Agency Classification

CENELEC EN 50575 compliant, Declaration of Performance (DoP) available

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

