## 1-1154036-7 | BUDI-1S-TB-16-S2-48-E-S



BUDI™ Fiber Optic Wall mount Enclosure, 16 SC/APC adapters, single element FIST splice trays for 48 SMOUV splices

- Compact, wall mountable fiber enclosures for indoor and outdoor use
- Specifically designed for fast FTTH deployment and easy customer connection
- Available with splicing (FIST) and/or patching and/or splitter combinations
- Multiple and modular wrap around cable port sealing options

#### **OBSOLETE**

#### **Product Classification**

Regional Availability EMEA

Product Type Fiber wall box

Product Brand BUDI™
Product Series BUDI-1S

#### General Specifications

Functionality Patching | Splicing

Access Front
Enclosure Color Gray

Front Cover Type Snap-on cover

InterfaceSC/APCLock TypeKey lockMountingWallPort, quantity16

**Splice Tray Construction** SE (Single element)

Splicing Capacity, maximum 48

#### Dimensions

 Height
 340 mm | 13.386 in

 Height, with cover
 420 mm | 16.535 in

 Width
 240 mm | 9.449 in

 Depth
 120 mm | 4.724 in

Page 1 of 3




## 1-1154036-7 | BUDI-1S-TB-16-S2-48-E-S

Cable Length m

Outer Cable Diameter mm

### Dimension Drawing



#### Material Specifications

**Enclosure Material Type**LSZH thermoplastic

**Optical Specifications** 

**Fiber Mode** Singlemode

#### **Environmental Specifications**

Environmental Space Indoor/Outdoor

**Qualification Standards** IEC 60529, IP54 | IEC 61753-1, category G

## Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

### Regulatory Compliance/Certifications

Agency Classification

**COMMSCOPE®** 

# 1-1154036-7 | BUDI-1S-TB-16-S2-48-E-S

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

