# 760049452 | VP360-12U-96P



### GigaSPEED X10D® VisiPatch® 360 12U Patch Panel Kit

### **Product Classification**

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio SYSTIMAX®

**Product Type** Back mount frame kit

Product Brand VisiPatch®

## General Specifications

Product Design VisiPatch® 360

ANSI/TIA Category 6A

#### Dimensions

 Height
 538.48 mm | 21.2 in

 Width
 215.9 mm | 8.5 in

 Depth
 287.02 mm | 11.3 in

## **Environmental Specifications**

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Safety Standard Austel | CE | UL | cUL

## Packaging and Weights

Included Back panel | Ninety-six connecting blocks | Twelve label holders | Twelve white labels | Twelve

wiring block covers | Twelve wiring blocks

Packaging quantity 1

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

**COMMSCOPE®** 

# 760049452 | VP360-12U-96P

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant





