760242455 | EPX-1U-MOD-DRW (AGL-1U-DRW-SL)



EPX 1U sliding drawer panel, accepts (4) G2 modules or adapter packs providing up to 48 duplex LC or 32 MPO ports

Product Classification

| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
|-----------------------|---|
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |
| Product Series | EPX |

General Specifications

| Application | Accepts four G2 modular cassettes |
|-------------------|-----------------------------------|
| Color | Black |
| Intelligence Type | Not iPatch® ready |
| Interface, front | Unloaded |
| Rack Type | EIA 19 in |
| Rack Units | 1 |
| Shelf Movement | Sliding |

Dimensions

| Height | 43.85 mm 1.726 in |
|--------|---------------------|
| Width | 482 mm 18.976 in |
| Depth | 250 mm 9.843 in |

Material Specifications

| Finish | Powder coated |
|---------------|---------------|
| Material Type | Steel |

Environmental Specifications

Safety Standard

UL

Packaging and Weights

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 16, 2023

COMMSCOPE°

760242455 | EPX-1U-MOD-DRW (AGL-1U-DRW-

Packaging quantity

Weight, net 1.512 kg | 3.333 lb

Regulatory Compliance/Certifications

1

Agency

 $(|\rangle$

Classification

CHINA-ROHS

REACH-SVHC

ROHS

UK-ROHS





Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 16, 2023

