

# 881546-000 | OCM1-CMB27AL2



OCM1 LGX Fiber Optic Module, CWDM, Mux, LC/APC, 8 channels, upgrade port, starting wavelength 1270 nm

## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	CWDM module
<b>Product Series</b>	LGX   OCM1

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Multiplexing
<b>Technology Type</b>	Thin film filter (TFF)
<b>Application</b>	For use with LGX panels
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	8-channel CWDM
<b>Interface, front</b>	LC/APC
<b>Interface, Input</b>	LC/APC
<b>Interface, Output</b>	LC/APC
<b>Multiplexers, quantity</b>	1
<b>Port Type, optional</b>	Upgrade port

## Dimensions

<b>Height</b>	129.54 mm   5.1 in
<b>Width</b>	27.94 mm   1.1 in
<b>Depth</b>	127 mm   5 in

## Optical Specifications

<b>Channel Spacing</b>	Skipped channels
<b>Starting Wavelength</b>	1270 nm

## Packaging and Weights

**Packaging quantity** 1  
**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

