MX6-SPL6030-1440-D



OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit down, Putty white, 2.2 mts

Alternative products available:

MX6-SPL6030-A-D7Z4 OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit down, Putty white, 7 ft

Product Classification

Regional Availability Australia/New Zealand | EMEA | Latin America | North America

Product Type Fiber entrance cabinet

Product Brand OMX600®

Product Series OMX

General Specifications

AccessFrontCable Entry LocationBottomCable Exit LocationBottomColorPutty white

Mounting Raised floor

Splice Trays Included, quantity 0

Splicing Capacity Note up to 5184 ribbon fibers

Splicing Capacity, maximum 5184

Dimensions

 Height
 2200 mm | 86.614 in

 Width
 600 mm | 23.622 in

 Depth
 300 mm | 11.811 in

Environmental Specifications

Environmental Space Indoor

COMMSCOPE®

MX6-SPL6030-1440-D

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

