



FIST Oval port seal kit for single fiber loose tube cable

- For sealing two cables having a diameter range of 12-25 mm through the oval outlet port (numbered 1-2) of the closure
- Included plastic sleeve stores the uncut loose buffer tubes between the 2 UMS profiles

Product Classification

| | |
|------------------------------|-------------------------|
| Regional Availability | EMEA |
| Product Type | Heat shrink sealing kit |
| Product Series | FIST-GC02 |

General Specifications

| | |
|--------------------------------|---------------------------------------|
| Application | For use with FIST-GC02 Fiber closures |
| Cable Capacity, maximum | 1 |
| Color | Black |

Dimensions

| | |
|---------------------------------------|------------------|
| Single Cable Diameter, maximum | 25 mm 0.984 in |
| Single Cable Diameter, minimum | 12 mm 0.472 in |

Packaging and Weights

| | |
|---------------------------|---|
| Included | Cable termination brackets Dummy plugs Multi-out gel seal |
| Packaging quantity | 1 |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|---|
| CHINA-ROHS | Below maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

