



Shielded Panel Frame, UCP Quick-Fit, 1U, Black

- Preferred replacement when used with MRJ21 and ACO applications

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Patch panel
Product Series	SL Series

General Specifications

Application	For use with UCP Quick Fit modules
Color	Black
Modules, quantity	4
Panel Style	Straight
Rack Type	EIA 19 in
Rack Units	1

Dimensions

Height	43.8 mm 1.724 in
Width	482.6 mm 19 in
Depth, with cable management	240.5 mm 9.469 in

Material Specifications

Material Type	Galvanised and powder-coated steel
----------------------	------------------------------------

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0

760239400 | CPP-QF-1U-E

Safety Standard

UL | cUL

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

