## 760239401 | CPPR-QF-1U-E



## Shielded Recessed Angled Panel Frame, UCP Quick-Fit, 1U, Black

• Preferred replacement when used with MRJ21 and ACO applications

### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Patch panel
Product Series SL Series

## General Specifications

**Application** For use with UCP Quick Fit modules

Color Black
Modules, quantity 4

Panel Style Angled recessed

Rack Type EIA 19 in

Rack Units 1

#### Dimensions

 Height
 43.8 mm | 1.724 in

 Width
 482.6 mm | 19 in

 Depth, with cable management
 270 mm | 10.63 in

## Material Specifications

Material Type Galvanised and powder-coated steel

## **Environmental Specifications**

Operating Temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Page 1 of 2



# 760239401 | CPPR-QF-1U-E

**Relative Humidity** Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

