SSC-760236966E2 | 12 in Pole Top for Ericsson



Top of Pole 12in Dia Concealment Enclosure for up to three Ericsson 220x /440x radios

- Enclosure for holding up to 3 metro cell radios directly below a multiband canister antenna
- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures
- Matching light pole or monopole options available

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your CommScope Representative for exact model number.

-Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

Mounts directly to CommScope poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

Product Classification

Portfolio CommScope®

Product Type Pole top
Product Brand Metro Cell

Ordering Note CommScope® standard product with terms

Warranty One year

General Specifications

Antenna Compatibility, CommScope CommScope Canister Antennas

Antenna Compatibility, Other Vendors ACE | AMPHENOL | DK | GALTRONICS | GAMMA

NU | JMA | KATHREIN | KMW | ROSENBERGER

Antennas Included None

Color Light Gray (RAL 7035)

Color Options Beige-Grey (RAL 7006) | Black (RAL 9005) | Black Green (RAL 6012) | Brown

(RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Signal

Black (RAL 9004) | Umbra Grey (RAL 7022) | White (RAL 9010)

Cooling Passive Cooling

Mounting Options Non-tapered poles | Tapered poles | Wood poles

Radio Compatibility, Ericsson 220x | 440x

Radios Included None

Dimensions



SSC-760236966E2 | 12 in Pole Top for Ericsson

 Height
 762 mm | 30 in

 Width
 304.8 mm | 12 in

Depth 304.8 mm | 12 in

Mounting Bolt Circle Diameter 142.748 mm | 5.62 in | 241.3 mm | 9.5 in

Material Specifications

Finish Aluminum Chromate
Finish Concealment Covers Powder coated

Material Type Aluminum | Steel

Environmental Specifications

Thermal Compliance GR-487

Packaging and Weights

Volume 0.056 m³ | 1.97 ft³ **Weight (unloaded)** 18.144 kg | 40 lb

* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

