F1-PNRNR

Base Product



FSJ1-50A Jumper with interface types N Male Right Angle and N Male Right Angle, variable length

Product Classification

Product Type Wireless transmission cable assembly

Product Series FSJ1-50A

General Specifications

Attachment, Connector A Field attachment

Attachment, Connector B Field attachment

Body Style, Connector ARight angleBody Style, Connector BRight angleInterface, Connector AN MaleInterface, Connector BN MaleOrientation0°Specification Sheet Revision LevelA

Variable Length For custom lengths contact 828-324-2200 or 1-800-982-1708 (toll free), or your local

CommScope representative

Dimensions

 Length
 0 m | 0 ft

 Nominal Size
 1/4 in

VSWR/Return Loss

Frequency Band VSWR Return Loss (dB)

700–3000 MHz 1.43 15.04

Jumper Assembly Sample Label



F1-PNRNR



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system