1-2055334-0 | OCP-L2-02MASEN-XX-YE



Fiber Optic Pigtail, Simplex, Singlemode, LC/APC to Stub, 0.9 mm diameter, 2 m

Product Classification

Regional Availability EMEA

Product Type Fiber pigtail, jacketed

Product Series OCP

General Specifications

Connector A, quantity 1

Color, boot AGreenColor, connector AGreenInterface, Connector ALC/APCJacket ColorYellow

Total Fibers, quantity 1


Dimensions

Cord Length 2 m | 6.562 ft

Ordering Tree



1-2055334-0 | OCP-L2-02MASEN-XX-YE



⁻ Standard Configuration by default 900µm buffer

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A1, TeraSPEED®

Environmental Specifications

Environmental Space Low Smoke Zero Halogen (LSZH)

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification CHINA-ROHS Above maximum concentration value ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



buffer color : yellow

²⁵⁰ µm color : natural or milky white