


# 11805C

---



Fixed-tuned UG-595/U for elliptical waveguide 180

## Product Classification

**Product Type** Elliptical waveguide connector

## General Specifications

**Attachment Method** Tab-flare | Tool-flare

**Body Style** Straight, fixed-tuned

**Inner Contact Plating** Unplated

**Interface** UG-595/U

**Outer Contact Plating** Unplated

**Pressurizable** Yes

## Dimensions

**Width** 38.1 mm | 1.5 in

**Length** 64.262 mm | 2.53 in

**Transition Length** 26.924 mm | 1.06 in

**Waveguide Size** WR42 | WG20 | R220

## Electrical Specifications

**Insertion Loss, typical** 0.01 dB

**Operating Frequency Band** 17.7 – 19.7 GHz

**Peak Power at Frequency, maximum** 7.30 kW @ 18.70 GHz

## Material Specifications

**Material Type** Brass

# 11805C

---

## Environmental Specifications

**Operating Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

**Storage Temperature** -55 °C to +85 °C (-67 °F to +185 °F)

## Packaging and Weights

**Weight, net** 0.4 kg | 0.882 lb

## Regulatory Compliance/Certifications

### Agency

ISO 9001:2015



### Classification

Designed, manufactured and/or distributed under this quality management system

## \* Footnotes

**Insertion Loss, typical** 0.05v<sup>-</sup>freq (GHz) (not applicable for elliptical waveguide)