## 4-1375191-2 | ECO SL110-5E-BK-24



SL-Series Modular Jack, RJ45, Cat5e Unshielded, Black (24 ea/pkg)

## Product Classification

CommScope®
Modular jack
SL Series
5e
Unshielded
Black
Solid   Stranded
None
SL Series faceplates and panels
Color matches with SL-style Black Faceplates and Surface Mount Boxes
Standard
200 times
SL Termination tool
IDC
ANSI/TIA-568-C.2   ISO/IEC 11801 Class D
T568A   T568B
14.78 x 20.07 mm (0.58 x 0.79 in)
1.6 mm   0.063 in
16.26 mm   0.64 in
14.48 mm   0.57 in

Page 1 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 26, 2024



## 4-1375191-2 | ECO SL110-5E-BK-24

Depth	30.48 mm   1.2 in
Compatible Insulated Conductor Diameter, maximum	1.45 mm   0.057 in
Contact Plating Thickness	1.27 μm
Compatible Conductor Gauge, solid	24-22 AWG
Compatible Conductor Gauge, stranded	26-24 AWG
Electrical Specifications	
Remote Powering	Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002
PoE Durability	Supports IEEE 802.3bt Type 4 (90 W) applications after 3000 plug to jack mating cycles
Safety Voltage Rating	150 Vac
Material Specifications	
Contact Base Material	Beryllium copper
Contact Plating Material	Gold
Material Type	Polycarbonate
Mechanical Specifications	
Plug Retention Force, minimum	89 N   20.008 lbf
Plug to Jack Mating Cycles	Complies to IEC 60603-7 series
Environmental Specifications	
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0
Safety Standard	CSA   cUL
Packaging and Weights	
Included	Strain relief cap
Packaging Material	Eco-friendly, single-use plastics-free
Packaging quantity	24
Packaging Type	Box   Carton
Regulatory Compliance/Certifications	
Agency Classification	

Agency

Classification

Page 2 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 26, 2024



## 4-1375191-2 | ECO SL110-5E-BK-24

CHINA-ROHS

REACH-SVHC

ROHS

**UK-ROHS** 



Below maximum concentration value

Compliant as per SVHC revision on www.commscope.com/ProductCompliance Compliant Compliant

Page 3 of 3

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 26, 2024

