# FGS-HTHR-5/8-12



## FiberGuide® Threaded Rod, 5/8in Diameter, 12in Length

## **Product Classification**

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type CommScope®

Threaded rod

Product Brand FiberGuide®

**Product Series** FGS

## General Specifications

**Color** Silver

Orientation Horizontal
Section Type Mounting

### **Dimensions**

 Length
 mm | 304.799 in

 Rod Length
 304.8 mm | 12 in

**Thread Size** 5/8 in

**System Dimensions** 102 mm x 102 mm (4 in x 4 in) | 102 mm x 152 mm (4 in x 6 in) | 51 mm x 152 mm (2 in x 6 in)

# Ordering Tree



# FGS-HTHR-5/8-12

#### **Rod Diameter**

9	1/2	1/2 in	
	5/8	5/8 in	
	12 MM	12 mm	
	14 MM	14 mm	
	16 MM	16 mm	

<sup>\*</sup> Rod diameter and length needs to be both metric or imperial sized

#### **Rod Length**

10	12	12 in
10	30	30 in
	48	48 in
	72	72 in
	30CM	30 cm
	75CM	75 cm
	180CM	180 cm

## Packaging and Weights

**Weight, net** 0.304 kg | 0.67 lb

## Regulatory Compliance/Certifications

### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

