

# Audio/Video (A/V) performance that's impossible to miss

Uniprise infrastructure solutions

North America



# Simple architecture. Reliable performance. Adaptable scalability.

### CommScope's Uniprise portfolio is the foundation of a smarter A/V network.

From boardrooms to classrooms, from pews to point-of-sale, and from hotel suites to exhibition halls, we are conveying information more visually than ever, and it's easy to see why. It's a fast, effective way to share what you need to be seen—to enlighten, alert, entertain, inspire or just set a mood.

To present your AVV network's best face, you need to embrace the latest capabilities and most exciting new technologies—and that takes a foundation built on the best copper and fiber-optic cabling infrastructure to carry it all. It has to be simple to deploy, deliver reliable performance, and adapt to meet the challenges of tomorrow's indispensable applications.

### Uniprise is the answer to your A/V challenge.

CommScope's globally-trusted Uniprise portfolio of solutions unlocks the potential of your A/V capabilities on a converged IT network. This simpler architecture streamlines deployment and administration, all while providing reliable operation and adaptable scalability that's ready to support new devices and new standards right out of the box.

More efficient deployments. Streamlined management. Future-ready performance. Exceptional user experiences. They're all possible with Uniprise, and CommScope is the only partner who provides such a diverse and complete portfolio of solutions, expertise and support, all under one roof.

From boardrooms to classrooms, from pews to point-of-sale, and from hotel suites to exhibition halls, we are conveying information more visually than ever, and it's easy to see why.



### Uniprise connects people to better A/V experiences just about anywhere.

In big ways and small, AV is part of our modern landscape everywhere we work, play and live. With Uniprise as its foundation, your AV network will be an enriching one, no matter the application:



### Office environments

- · Conference rooms
- · Training centers
- Huddle and collaboration spaces



### Schools & places of worship

- Classroom presentations
- · Auditorium sound and projection
- · PA systems



### **Hospitality settings**

- · In-room entertainment
- · Lobby monitors and interactive maps
- · Bluetooth-connected network devices



### Retail

- Digital signage and video monitors
- · PoS terminals and VoIP telephony
- · Inventory control

**Uniprise** delivers the simple, reliable, adaptable performance modern A/V networks need—in every setting, for every need.


# Uniprise is built for the challenges of advanced A/V network requirements:

- · Simplified, IT-convergent architecture
- · Reliable, robust performance
- · Adaptability to handle diverse applications and services
- Concealable cable and connections
- · Future-ready bandwidth and speed



# Audio/Video Architecture

CommScope builds copper and fiber infrastructure solutions that deliver on the full potential of audio/video applications; simplifying the architecture by converging A/V with IT, providing reliable, secure network access anywhere on the property, and adaptable enough to deliver today's highest resolutions—and tomorrow's—with ease.




# Copper Cables



## **Shielded Copper Cables**

Material ID	Product Number	Description
UN874028604/10	CS44P BLK C6A 4/23 F/UTP RL 1KFT	CS44P ETL verified Category 6A F/UTP cable, plenum, black jacket, 4 pair count, 1000 ft. (305 m) length reel
UN874028404/10	CS34P BLK C6 4/23 F/UTP RL 1KFT	CS34P ETL verified Category 6 F/UTP cable, plenum, black jacket, 4 pair count, 1,000 ft. (305 m) length reel
UN884018204/10	CS34R BLK C6 4/23 F/UTP RL 1KFT	CS34R ETL verified Category 6 F/UTP cable, plenum, black jacket, 4 pair count, 1,000 ft. (305 m) length reel



# **Unshielded Copper Cables**

Material ID	Product Number	Description
UN874021414/10	CS44P BLK C6A 4/23 U/UTP CPK 1KFT	CS44P ETL verified Category 6A U/UTP cable, plenum, black jacket, 4 pair count, 1000 ft. (305 m) length CommPak
UN884032614/10	CS44R BLK C6A 4/23 U/UTP CPK 1KFT	CS44R ETL verified Category 6A U/UTP cable, non-plenum, black jacket, 4 pair count, 1,000 ft. (305 m) length CommPak
UN874047214/10	CS34P BLK C6 4/23 U/UTP CPK 1KFT	CS34P ETL verified Category 6 U/UTP cable, plenum, black jacket, 4 pair count, 1,000 ft. (305 m) length CommPak
UN884020514/10	CS34R BLK C6 4/23 U/UTP CPK 1KFT	CS34R ETL verified Category 6 U/UTP cable, non-plenum, black jacket, 4 pair count, 1,000 ft. (305 m) length CommPak

# Copper Panels



## **Shielded Copper Panels**

Material ID	Product Number	Description
760237046	CPP-SDDM-SL-1U-24	CommScope Discrete Distribution Module Panel, SL, STP, 1U, 24 port
760237047	CPP-SDDM-SL-2U-48	CommScope Discrete Distribution Module Panel, SL, STP, 2U, 48 port
760237048	CPPA-SDDM-SL-1U-24	CommScope Angled Discrete Distribution Module Panel, SL, STP, 1U, 24 port
760237049	CPPA-SDDM-SL-2U-48	CommScope Angled Discrete Distribution Module Panel, SL, STP, 2U, 48 port
760237050	CPPR-SDDM-SL-1U-24	CommScope Recessed Angled Discrete Distribution Module Panel, SL, STP, 1U, 24 port
760237051	CPPR-SDDM-SL-2U-48	CommScope Recessed Angled Discrete Distribution Module Panel, SL, STP, 2U, 48 port
760237066	CPP-6A-SDDM-SL-1U-48	Commscope Discrete Distribution Module Panel, Category 6A, SL, STP, 1U, 48 port
760237067	CPP-6-SDDM-SL-1U-48	Commscope Discrete Distribution Module Panel, Category 6, SL, STP, 1U, 48 port



# **Unshielded Copper Panels**

Material ID	Product Number	Description
760180042	UNP-6-DM-1U-24	Uniprise Distribution Module Panel, Category 6, UTP, 1U, 24 port
760180059	UNP-6-DM-2U-48	Uniprise Distribution Module Panel, Category 6, UTP, 2U, 48 port
760180067	UNPA-6-DM-1U-24	Uniprise Angled Distribution Module Panel, Category 6, UTP, 1U, 24 port
760180075	UNPA-6-DM-2U-48	Uniprise Angled Distribution Module Panel, Category 6, UTP, 2U, 48 port
760162800	UNP-6A-DM-1U-24	Uniprise Distribution Module Panel, Category 6A, UTP, 1U, 24 port
760162818	UNP-6A-DM-2U-48	Uniprise Distribution Module Panel, Category 6A, UTP, 2U, 48 port
760162826	UNPA-6A-DM-1U-24	Uniprise Angled Distribution Module Panel, Category 6A, UTP, 1U, 24 port
760162834	UNPA-6A-DM-2U-48	Uniprise Angled Distribution Module Panel, Category 6A, UTP, 2U, 48 port
760207274	CPP-UDDM-M-1U-24	CommScope Discrete Distribution Module Panel, M-series, UTP, 1U, 24 port
760207282	CPP-UDDM-M-2U-48	CommScope Discrete Distribution Module Panel, M-series, UTP, 2U, 48 port



## **Shielded Copper Information Outlets**

Material ID	Product Number	Description
760238139	USL600-SHLD, BLK	Uniprise SLX Series modular information outlet, Category 6, shielded , 4 Pair, without dust cover, black
760238148	USL600-SHLD-DC, BLK	Uniprise SLX Series modular information outle, Category 6, shielded , 4 Pair, with dust cover, black
760238121	USL10G-SHLD, BLK	Uniprise SLX Series modular information outle, Category 6A, shielded, 4 pair, without dust cover, black
760238130	USL10G-SHLD-DC, BLK	Uniprise SLX Series modular information outle, Category 6A, shielded, 4 pair, with dust cover, black



## **Unshielded Copper Information Outlets**

Material ID	Product Number	Description
760237777	UNJ600-BK	Uniprise modular information outlet, RJ45, Category 6, T568A/T568B, U/UTP, without dust cover, black
760237789	UNJ600-BK-100PK	Uniprise modular information outlet, RJ45, Category 6, T568A/T568B, U/UTP, without dust cover, black, 100 pack
760241173	UNJ10G-BK	Uniprise UNJ Series modular information outlet, RJ45, Category 6A, U/UTP, without dust cover, black



## **Shielded Copper Patch Cords**

Material ID	Product Number Description	
UC111F2-01	SFTP-PC6-BK	Uniprise Category 6 S/FTP Patch Cord, RJ45 to RJ45, 4-pair, Non-Plenum, Black Jacket
UC111G2-01	SFTP-PC6A-BK	Uniprise Ultra 10 Category 6A S/FTP Patch Cord, RJ45 to RJ45, 4-pair, Non-Plenum, Black Jacket



### **Unshielded Copper Patch Cords**

Material ID	Product Number	Description
UC1BBB2-01	UNC6-BK	Uniprise Category 6 U/UTP Patch Cord, RJ45 to RJ45, 4-pair, Non-Plenum, Black Jacket
UC1AAA2-01	UNC6A-BK	Uniprise Ultra 10 Category 6A U/UTP Patch Cord, RJ45 to RJ45, 4-pair, Non-Plenum, Black Jacket



## **Under Carpet Solutions**

Material ID	Product Number	Description	
1375045-3		Undercarpet flush surface wall mounting box and cover, gray	
1499539-5	TE610UC-WT100	Undercarpet copper cable, Category 6, 4-pair, 8 conductors, U/UTP, 100 ft., white	
1933377-1		Undercarpet SL series modular jack data kit, Category 6, floor, surface, black	
2111682-1		Undercarpet communications Category 5e/Category 6 transition wiring block	
3-553079-3		Undercarpet flat copper cable, 3 conductors, 12 AWG, shielded, 50 ft., white/green/black	
553095-1		Undercarpet flush wall frame cover for communications transition box	
553481-1		Undercarpet hold down tape, 180 ft., gray	
553536-3		Undercarpet top shield accessory, 50 ft.	
553739-2		Undercarpet flush wall frame communications transition box	
554123-3		Undercarpet floor preparation, 50 ft., yellow	
554192-1		Undercarpet DCR kit, 3-conductor, double duplex, black	
554862-1		Undercarpet power transition block, 3 or 5-conductor	
555287-1		Undercarpet low-profile communications floor fitting, 4 ports, black	
6-553453-2		Undercarpet spray adhesive, 1 package, clear	



# Ceiling Connector Assembly

Material ID Product Number		Description
760235587	CCA-CAT6-PLENUM-BLACK-N018	Category 6 U/UTP cord, plenum, RJ45 to ceiling connector, 1.5 ft, black
760235591	CCA-CAT6A-PLENUM-BLACK-N018	Category 6A U/UTP cord, plenum, RJ45 to ceiling connector, 1.5 ft, black



### Mini-pod

Material ID	Product Number	Description
2153216-3	MINIPOD,UNLOADED,3PORT,W/ANGL ADP, UTP	MiniPod, Category 6, 3 port, unloaded with angled adapters, U/UTP
2153216-4	MINIPOD,UNLOADED,4PORT W/ANGL ADP,UTP	MiniPod, Category 6, 4 port, unloaded with angled adapters, U/UTP
2153216-6	MINIPOD,UNLOADED,6PORT W/ANGL ADP,UTP	MiniPod, Category 6, 6 port, unloaded with angled adapters, U/UTP



# Field Terminated RJ45 Modular Plug

Material ID	Description
760244127	FIELD TERM RJ45 MP C6A, PACK OF 25
760244128	FIELD TERM RJ45 MP C6, PACK OF 25
760244129	FIELD TERM RJ45 MP C6A, BAG OF 100
760244130	FIELD TERM RJ45 MP C6, BAG OF 100
760244131	FIELD TERM RJ45 MP C6A, BAG OF 100 +TOOL
760244132	FIELD TERM RJ45 MP C6, BAG OF 100 +TOOL
760244091	FIELD TERM ANTI-SNAG CLIP CLR BAG OF 50
760244092	FIELD TERM ANTI-SNAG CLIP ALM BAG OF 50
760244093	FIELD TERM ANTI-SNAG CLIP BLK BAG OF 50
760244094	FIELD TERM ANTI-SNAG CLIP WH BAG OF 50
760244095	FIELD TERM ANTI-SNAG CLIP GY BAG OF 50
760244096	FIELD TERM ANTI-SNAG CLIP OR BAG OF 50
760244097	FIELD TERM ANTI-SNAG CLIP BL BAG OF 50
760244098	FIELD TERM ANTI-SNAG CLIP RD BAG OF 50
760244099	FIELD TERM ANTI-SNAG CLIP YL BAG OF 50
760244100	FIELD TERM ANTI-SNAG CLIP GN BAG OF 50
760244101	FIELD TERM ANTI-SNAG CLIP VT BAG OF 50



## Faceplates

Material ID	Product Number	Description
2111009-2	FP KT,LBL,SGL GNG,2P,SL.BLK	Faceplate kit, labeled, 1 gang, 2 port, vertical orientation, black
2111011-2	FP KT,LBL,SGL GNG,4P,SL,BLK	Faceplate kit, labeled, 1 gang, 4 port, vertical orientation, black

# Fiber Optic Patch Cord Configurator



















### Prefix

1	FD	Jumper - plenum
2	FF	Jumper - Dual Rated (LSZH/Riser)

### Connector 2

	LC	LC standard
6	LA	LC angled
7	SC	SC standard
	SA	SC angled

### Jacket color

11	J	Yellow
11	М	Aqua

### Fiber type

3	Χ	LazrSPEED® 550 multimode
5	W	TeraSPEED® singlemode

8	2	1.6 mm simplex
	4	1.6 mm zipcord

### Breakout length

		_
12	Х	No breakout

### Connector 1

	LC	LC standard
4	LA	LC angled
5	SC	SC standard
	SA	SC angled

### Cordage size

8	2	1.6 mm simplex
	4	1.6 mm zipcord

### Unit of measurement

13	F	Feet
	М	Meter

### Fiber count

	1	1 fiber
9	2	2 fiber

### Length

Lengan		
14	2-999	Feet
16	1-999	Meters

LC keyed fiber patchcords are also available as part of CommScope secure fiber solutions.

# Fiber Optic Patch Cord Configurator













0.9 mm (Tight buffered fiber BTW)

0.9 mm (SBJ cordage





### Prefix

1	FA	Pigtail tight buffer
2	FB	Pigtail - Riser SBJ

### Connector 2

Cordage size

6 7	UC	Unconnectorized

### Jacket color

	А	Blue
	В	Orange
	С	Green
	D	Brown
	Е	Slate
11	G	Red
	Н	Black
	J	Yellow
	K	Violet
	L	Rose
	М	Aqua
	Х	KIT pigtail

### Fiber type

Connector 1

0	Х	LazrSPEED® 550 multimode
W TeraSP	TeraSPEED® singlemode	

LC standard LC angled SC standard SC angled

### Fiber count

1 100	er court	
9	1	1 fiber
	А	6 fiber pigtail kit BL-WH (1-6)
	В	6 fiber pigtail kit RD-AQ (7-12)
	С	12 fiber pigtail kit BL-AQ (1-12)

### Breakout length

12	X	No breakout
----	---	-------------

### LC keyed fiber pigtails are also available as part of CommScope secure fiber solutions.

### Unit of measurement

13	F	Feet
	М	Meter

### Length

14	1-23	Feet
16	1-7	Meters

CommScope pushes the boundaries of communications technology with game-changing ideas and ground-breaking discoveries that spark profound human achievement.

We collaborate with our customers and partners to design, create and build the world's most advanced networks. It is our passion and commitment to identify the next opportunity and realize a better tomorrow. Discover more at commscope.com

# **COMMSCOPE®**

### commscope.com

Visit our website or contact your local CommScope representative for more information.

© 2020 CommScope, Inc. All rights reserved.

Unless otherwise noted, all trademarks identified by or TM are registered trademarks, respectively, of CommScope, Inc. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services. CommScope is committed to the highest standards of business integrity and environmental sustainability with a number of CommScope's facilities across the globe certified in accordance with international standards, including ISO 9001, TL 9000, and ISO 14001.

Further information regarding CommScope's commitment can be found at <a href="https://www.commscope.com/About-Us/Corporate-Responsibility-and-Sustainability">www.commscope.com/About-Us/Corporate-Responsibility-and-Sustainability</a>.