


# 6-554720-5 | MP-88U-F-2



Modular Plug, 8P/8C, unshielded, flat oval, 8-position, category 5, Indonesia, 50 pcs

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

CommScope®

### Product Type

Modular plug

## General Specifications

### ANSI/TIA Category

5

### Cable Type

Flat oval, unshielded

### Conductor Type

Solid | Stranded

### Interface

RJ45

### Positions/Loaded Contacts

8/8

### Termination Type

IDC

## Dimensions

### Compatible Cable Diameter, maximum

8.89 mm | 0.35 in

### Compatible Cable Diameter, minimum

2.54 mm | 0.1 in

### Compatible Insulated Conductor Diameter, maximum

0.99 mm | 0.039 in

### Compatible Insulated Conductor Diameter, minimum

0.86 mm | 0.034 in

### Contact Plating Thickness

1.27 µm

### Compatible Conductor Gauge, solid

26–24 AWG

### Compatible Conductor Gauge, stranded

26–24 AWG

## Electrical Specifications

### Current Rating, maximum

0.75 A

### Insulation Resistance, minimum

500 mOhm

# 6-554720-5 | MP-88U-F-2

---

**Safety Voltage Rating** 150 Vac

## Material Specifications

**Contact Base Material** Phosphor Bronze

**Contact Plating Material** Gold

**Material Type** Glass filled polycarbonate

## Mechanical Specifications

**Plug Insertion Life, minimum** 750 times

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)

**Relative Humidity** Up to 93%, non-condensing

**Flammability Rating** UL 94 V-2

**Safety Standard** UL 1863

## Packaging and Weights

**Packaging quantity** 50

**Packaging Type** Bag | Box | Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

