760248005 | OCAB-P-S1-01



OCAB Outdoor fiber distribution cabinet

- OCAB is an all-purpose metal outdoor cabinet optimized solution to accommodate the 19 inch FACT and MFPS shelf product families
- OCAB cabinets offers dust-proof, environmental and mechanical protection for the fiber management functions of splicing, patching and passive component integration
- Serves as a cross-connect or interconnect cabinet with any combination of spliced and connectorized splitters
- A swing handle with half cylinder lock and 3 point latch system prevents unauthorized access
- The standard included base allows easy entry, fixation, identification and sealing of the cables
- Usable 19-inch panel-height is 18 RU
- Anti-vandalism features such as IK10 stainless steel material rating, reinforced door hinges preventing door removal and anti-graffiti paint finish (optional)
- Easy installable and wingnut-secured in-let plates can be custom-configured, selecting the amount of incoming, outgoing ports and PG gland sizes
- Removable top roof for possible future upgrades
- Possibility for infield repair, removable cabinet body
- Various accessories such as plinths and in-ground roots

Product Classification

Regional Availability EMEA

Product Type Fiber cross-connect hub

Product Series OCAB

General Specifications

Access Front | Single door

Color Light Gray (RAL 7035)

Lock Type Swivel with half cylinder lock (EURO DIN)

Mounting In-ground root | Partially buried | Pre-fabricated base

Dimensions

 Height
 1301 mm | 51.221 in

 Width
 800 mm | 31.496 in

 Depth
 320 mm | 12.598 in

Enclosure Size Medium

Material Specifications

Finish Powder coated polyester

COMMSC PE°

760248005 | OCAB-P-S1-01

Material Type Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

Environmental Specifications

Environmental Space Above ground

Qualification Standards IEC 60529, IP55 | IK10

Packaging and Weights

Included Base with covers | Blank cable inlet plate | Cable inlet plate with 6 PG21 blind plugs | Mounting

profiles for shelves

Packaging quantity 2
Packaging Type Pallet

Note Two cabinets supplied per Euro pallet, bolted and shrink wrapped in polythene with cardboard hosing

protection strapped together for secure shipping

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

