760248007 | OCAB-P-S2-01



OCAB Outdoor fiber distribution cabinet

- OCAB is an all-purpose metal outdoor cabinet optimized solution to accommodate the 19 inch FACT and MFPS shelf product families
- OCAB cabinets offers dust-proof, environmental and mechanical protection for the fiber management functions of splicing, patching and passive component integration
- Serves as a cross-connect or interconnect cabinet with any combination of spliced and connectorized splitters
- A swing handle with half cylinder lock and 3 point latch system prevents unauthorized access
- The standard included base allows easy entry, fixation, identification and sealing of the cables
- Usable 19-inch panel-height is 18 RU
- Anti-vandalism features such as IK10 stainless steel material rating, reinforced door hinges preventing door removal and anti-graffiti paint finish (optional)
- Easy installable and wingnut-secured in-let plates can be custom-configured, selecting the amount of incoming, outgoing ports and PG gland sizes
- Removable top roof for possible future upgrades
- Possibility for infield repair, removable cabinet body
- Various accessories such as plinths and in-ground roots

Product Classification

Regional Availability	EMEA
Product Type	Fiber cross-connect hub
Product Series	OCAB

General Specifications

Access	Front Single door
Color	Light Gray (RAL 7035)
Lock Type	Swivel with half cylinder lock (EURO DIN)
Mounting	In-ground root Partially buried Pre-fabricated base

Dimensions

Height	1601 mm 63.032 in
Width	800 mm 31.496 in
Depth	320 mm 12.598 in
Enclosure Size	Medium

Material Specifications

Finish

Powder coated polyester

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 2, 2023



760248007 | OCAB-P-S2-01

Material Type

Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

Environmental Specifications

Environmental Space	Above ground	
Qualification Standards	IEC 60529, IP55	IK10

Packaging and Weights

Included	Base with covers Blank cable inlet plate Cable inlet plate with 6 PG21 blind plugs Mounting profiles for shelves	
Packaging quantity	2	
Packaging Type	Pallet	
Note	Two cabinets supplied per Euro pallet, bolted and shrink wrapped in polythene with cardboard hosing protection strapped together for secure shipping	

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: October 2, 2023

