760242345 | SFC-LCAF-UNV-8X QWIK IITM LC



Qwik II® Field Installable LC Connector, Singlemode-APC, Green, for 0.25 /0.9/2.0/3.0 mm, single pack

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber connector

Product Brand Qwik II® | TeraSPEED®

Product Series Qwik II

General Specifications

Body StyleUniversalColor, bootBlackColor, housingGreen

Ferrule Geometry Factory polished

Interface LC/APC

Interface Feature Field Installable | Mechanical splice

Dimensions

Compatible Cable Diameter 0.25 mm | 0.01 in | 0.9 mm | 0.035 in | 2 mm | 0.079 in | 3 mm | 0.118 in

Material Specifications

Ferrule Material Zirconia

Optical Specifications

Fiber Mode Singlemode

Fiber TypeOS2Insertion Loss, maximum0.6 dBInsertion Loss, typical0.3 dB

Page 1 of 2

760242345 | SFC-LCAF-UNV-8X QWIK IITM LC

Return Loss, minimum

50 dB

Environmental Specifications

Operating Temperature $-40 \, ^{\circ}\text{C} \text{ to } +75 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F to } +167 \, ^{\circ}\text{F})$

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

AgencyClassificationCHINA-ROHSBelow maximum concentration valueISO 9001:2015Designed, manufactured and/or distributed under this quality management systemREACH-SVHCCompliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

