CLT4HM-1M-CO



MQ Multiport cluster 4 ports cable assembly with interface type MQ female to 4.3-10 male, size 1/4", length 1 meter

Product Classification

Product TypeWireless transmission cable assembly

Product Series MQ

Warranty Two years

General Specifications

Attachment, Connector A Factory attached

Attachment, Connector B Factory attached

Body Style, Connector AStraightBody Style, Connector BStraightInterface, Connector AMQ FemaleInterface, Connector B4.3-10 Male

Specification Sheet Revision Level A

Dimensions

Length 1 m | 3.281 ft

Nominal Size 1/4 in

Port Configuration

Pin Assignment	Label
1	MQ4-1 (R-)
2	MQ4-2 (CR-)
3	MQ4-3 (CL-)
4	MQ4-4(L-)



CLT4HM-1M-CO

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)	Insertion Loss, typical (dB)
0-2700 MHz	1.151	23.1	0.6
2700-4200 MHz	1.201	20.8	0.75
4200-6000 MHz	1.36	16.5	0.9

Mechanical Specifications

Minimum Bend Radius, multiple Bends25.4 mm | 1 inMinimum Bend Radius, single Bend25.4 mm | 1 in

Environmental Specifications

Operating Temperature $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$

Immersion Test Method IEC 60529, IP67

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



* Footnotes

Warranty For more information, please consult our Product Warranty guidelines

