# FGS-MD9E-F



## FiberGuide® 90° Down Elbow, 4 in x 12 in, yellow

## **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Elbow

Product Brand FiberGuide®

Product Series FGS

# General Specifications

Angle/Bend Direction90° downColorYellowOrientationVertical

Section Type Elbow section

#### **Dimensions**

 Height
 112 mm | 4.409 in

 Width
 347 mm | 13.661 in


 Length
 208 mm | 8.189 in

**System Dimensions** 102 mm x 305 mm (4 in x 12 in)

# Ordering Tree



# FGS-MD9E-F



#### **Section Color**



## Section Size

10	Α	4 x 4 in
	В	4 x 6 in
	С	2 x 2 in*
	F	4 x 12 in
	G	2 x 6 in

## Material Specifications

Material Type Engineering Thermoplastic

# **Environmental Specifications**

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0

Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

# Packaging and Weights

**Weight, net** 0.557 kg | 1.228 lb

## Regulatory Compliance/Certifications

### Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



<sup>\*</sup> FGS-MD9A-C or FGSB-MD9A-C