FGS-MDSA-FB



FiberGuide® Straight Reducer, 4x12 to 4x6in, Yellow

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Reducer

Product Brand FiberGuide®

Product Series FGS

General Specifications

ColorYellowOrientationHorizontalSection TypeReducer

Dimensions

 Height
 112 mm | 4.409 in

 Width
 347 mm | 13.661 in


 Length
 254 mm | 10 in

System Dimensions 102 mm x 152 mm (4 in x 6 in) | 102 mm x 305 mm (4 in x 12 in)


Ordering Tree



FGS-MDSA-FB



Section Color



Section Size

10	АВ	4 x 4 in to 4 x 6 in
	AC	4 x 4 in to 2 x 2 in
	C2C	2 x 2 in to dual 2 x 2 in
	F2B	4 x 12 in to dual 4 x 6 in
	FB	4 x 4 in to 4 x 6 in
	FB-L	4 x 12 in to left 4 x 6 in , black*
	FB-R	4 x 12 in to right 4 x 6 in , black*
	HF-L	4 x 24 in to left 4 x 12 in , black*
	HF-R	4 x 24 in to right 4 x 12 in, black*
	HF	4 x 24 in to 4 x 12 in
	GA	2 x 6 in to 4 x 4 in
	GB	2 x 6 in to 4 x 6 in

Material Specifications

Material Type Engineering Thermoplastic

Environmental Specifications

Flammability Rating CSA S143 | UL 2024 | UL 94 V-0
Halogen Characteristics Blue Angel | TCO '99 | WEEE

Safety Standard CSA | UL

Packaging and Weights

Weight, net 0.54 kg | 1.19 lb

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



^{*} Only comes in black

FGS-MDSA-FB



