## 131599-000 | FOSC-OC-6DSD120ANN2T-U23

FOSC® A-TRAY-24 type, DWDM, 16 channels, demux, 1561.42 nm starting wavelength, skipped channels

### **Product Classification**

Regional AvailabilityNorth AmericaProduct TypeDWDM splice tray

Product Brand FOSC®
Product Series FOSC-OC

## General Specifications

**Application** For use in FOSC closures

Interface, InputStub tailInterface, OutputStub tail

#### **Dimensions**

 Height
 233.68 mm | 9.2 in

 Width
 99.06 mm | 3.9 in

 Depth
 10.67 mm | 0.42 in

## Packaging and Weights

Packaging quantity

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

UK-ROHS Compliant/Exempted

COMMSC PE®

# 131599-000 | FOSC-OC-6DSD120ANN2T-U23



